# Product Information Sheet ARclean® W-3473



ARclean® W-3473 is a 2 mil (51  $\mu$ m) clear polyester release liner with an <u>easy release</u>, thermally cured silicone coating on one side. ARclean® W-3473 is formulated and designed with a smooth surface and high thickness constancy.

### **PRODUCT APPLICATIONS**

The typical use for this product is as a support and protection film for non-silicone pressure-sensitive adhesives (PSAs) and cast materials requiring an easy release on a smooth liner. ARclean® W-3473 is ideally suited for applications including specialty die-cut adhesives and labels, engineered tapes, skin-friendly adhesives, medical devices, and electronics.

#### **FEATURES AND BENEFITS**

- Easy release from PSAs, including acrylic, rubber, hot melt, hydrocolloids, and others
- Easy release from cast materials, including elastomers, foams, ceramics, and dispersions
- Smooth surface is ideal for use with optical-grade materials
- Narrow consistent release profile preventing adhesive confusion
- Stable release properties, no "lock-up", and consistent release force over time
- Green, environmentally friendly, solvent-free coating
- Excellent thermal stability, aging resistance, and anchorage to polyester base film
- Suitable for indirect skin and food contact, US FDA Drug Master File (21 CFR)
- Compatible with clean room applications



## **Product Information Sheet** ARclean® W-3473



.Technical Properties			
Attribute*	Typical Values*		Test Method*
Liner release (180°, 300 in/min, EL-8883 test tape)	22 g/2 in		ASTM D5375
Recommended storage of	70°F ± 20°F	21°C ± 11°C	
unconverted product	50% ± 20% RH	50% ± 20% RH	
Core type†	Fiber		
Wind†	Release coated side in		
Shelf life of unconverted product	Not to exceed eight months from date of manufacture		

<sup>\*</sup>All stated values are nominal and should only be used as a guide for selection. They are not specifications.

Note: The information contained on this data sheet is based upon test results of limited quantities of this material and may be modified by Adhesives Research following additional production experience and evaluation. This data should not be used in preparing specifications. Products identified as developmental may be subject to modification by Adhesives Research,

#### STORAGE OF LINERS

Customers should be aware of specific product shelf life. Shipping and storage conditions affect shelf life. The optimum storage temperature is 70°F (21°C). Cool, dry storage is

Consult your Adhesive Research sales representative if you need additional information.

This Product Information sheet ("PI Sheet") is not an offer to sell by Adhesives Research ("AR") and does not contain any binding warranties or terms of sale. While this PI Sheet does contain technical information and general warranty information, this PI Sheet is non-binding and is for information purposes only. If you wish to purchase the product set forth on this PI Sheet ("Product"), or have any questions regarding the warranty or other terms related to this Product, contact AR customer service or a sales representative and they will provide you with AR's terms of sale for the Product in the form of a Sales Order Acknowledgment. AR shall not be bound by any terms or information set forth in this PI Sheet.

#### DISCLAIMER OF WARRANTIES

AR's warranty on product is limited to the warranty set forth in the Sales Order Acknowledgment. NOTHING SET FORTH IN THIS PRODUCT INFORMATION SHEET SHALL CONSTITUTE A WARRANTY OF ANY KIND AND EXCEPT AS SET FORTH IN THE SALES ORDER ACKNOWLEDGMENT. UNLESS OTHERWISE STATED IN A SALES ORDER ACKNOWLEDGMENT, AR EXPRESSLY DISCLAIMS ALL WARRANTIES, INCLUDING THE WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. No provisions, statements, diagrams, drawings or pictures contained in any product literature, price list, catalogue, purchase order, product data sheet, order acknowledgment, invoice, delivery ticket, or any other communication by AR, including information on AR's website or statements made by AR's employees or agents, constitute express warranties. Results of tests and recommendations included in communications of AR do not constitute express warranties. MANY FACTORS MAY AFFECT THE USE AND PERFORMANCE OF AN AR PRODUCT IN A PARTICULAR APPLICATION, INCLUDING, AMONG OTHERS, THE PRODUCT SELECTED FOR USE, THE CONDITIONS IN WHICH THE PRODUCT IS USED, THE TIME AND ENVIRONMENTAL CONDITIONS IN WHICH THE PRODUCT IS EXPECTED TO PERFORM, THE MATERIALS TO BE USED WITH THE PRODUCT, THE SURFACE PREPARATION OF THOSE MATERIALS, AND THE APPLICATION METHOD FOR THE PRODUCT; THEREFORE, PURCHASER ACCEPTS RESPONSIBILITY FOR DETERMINING WHETHER AR'S PRODUCT IS FIT FOR A PARTICULAR PURPOSE AND SUITABLE FOR PURCHASER'S METHOD OF APPLICATION. AR retains the right to modify or change its products if in AR's judgment it is advisable.

AR limits the purchaser's remedies in the event of a breach of any warranty. The purchaser's exclusive remedy and AR's obligations for a breach of any warranty shall be as set forth in the Sales Order Acknowledgment.

ARcare®, ARclad®, ARclean®, ARflow®, ARclear® are registered trademarks of Adhesives Research, Inc. ARseal™ is a trademark of Adhesives Research, Inc. Adhesives Research is a registered service mark of Adhesives Research, Inc. for engineering and design services in the field of pressure-sensitive adhesive systems.

©2023 Adhesives Research, Inc. Printed in USA.

(21 November 2023)

North America - Headquarters Adhesives Research, Inc. 400 Seaks Run Road Glen Rock, PA 17327 Phone: +1 (717) 235-7979

Toll-free: +1 (800) 445-6240 Fax: +1 (717) 235-8320

#### Europe

Adhesives Research Ireland, Ltd. Raheen Business Park Raheen, Limerick V94 VH22 Ireland Phone: +353 61 300 300 Fax: +353 61 300 700

Adhesives Research China Co., Ltd. Room 2710-2711, Building B Far Glory International Square No. 317 Xianxia Road Shanghai, China 200051 Phone: +86 (21) 6150 4358 Fax: +86 21 6278 5576

#### Singapore

Adhesives Research PTE Ltd. 1 Paya Lebar Link #04-01 Paya Lebar Quarter 1 Singapore 408533 Phone: +65 6955 8528 Fax: +65 6777 7261

<sup>†</sup>Reflects master roll conformation.